



CeBeCo[®] SONDERMAT

Immersion cleaning system

- Made of thick welded steel or stainless sheet steel
- Available in 4 standard sizes as well as individual intermediate and special sizes
- For use with aqueous cleaners

CeBeCo® SONDERMAT

Function/Fields of use

The components to be washed lie on a movable sieve bottom inside the washing chamber and are immersed in and lifted out of the cleaning agent with the set number of strokes. Depending on the operating weight and customer-specific requirements, you can choose a gear, pneumatic or hydraulic lifting device.

Equipment

Direct electrical heater, insulation, digital thermostat, rim extraction, insertion cover.

Supplementary features

Increase of operating weight, surface exhaust, oil separator for non-emulsified oils in bypass mode, micro-filter in the bypass (depth filter), pneumatic lid, soil protection basin, drainage pump, weekly clock, side ledges.

Types

TYPE DESIGNATION	24/15	035	060	085
ACTUAL DIMENSIONS (LxWxH IN MM)	600 x 400 x 150	700 x 500 x 250	1000 x 600 x 250	1700 x 500 x 250

Model variants



The illustrations on this page show also special equipment that are not included in the standard scope of delivery. The contents comply with the status at the date of publication (03/16). We reserve the right to implement changes to construction and equipment. Screen colours only reproduce an approximation of the actual colour hue. Surcharge for the displayed special equipment.

Quality and Experience since 1932